

CORI-FLOW®

Precision Mass Flow Meters / Controllers for Liquids and Gases



Introduction

Bronkhorst Cori-Tech B.V. manufactures precise, compact Mass Flow Meters and Controllers for gases and liquids, based on the Coriolis measuring principle. The instruments are made to customers' specification, suitable for use in laboratory, for integration in manufacturing machines and pilot plants and even for application in industrial or hazardous areas.

CORI-FLOW® series direct mass flow meters and controllers

Bronkhorst, specialists in low flow measurement and control, designed the CORI-FLOW® series mass flow metering instruments to provide high accuracy in two classes: $\pm 0,2\%$ or $\pm 0,5\%$ of Reading.

CORI-FLOW® utilises a patented, advanced Coriolis type mass flow sensor to achieve unsurpassed performance, even with changing operating conditions in pressure, temperature, density, conductivity and viscosity. The instruments are offered as separate flow meters or with close-coupled control valve or pump, thus constituting a compact Coriolis-type mass flow controller. The instruments have analog (0-5 Vdc / 4-20 mA) and RS232 output as standard and can, as options, be equipped with interface to Profibus-DP®, DeviceNet™, Modbus-RTU or FLOW-BUS.

There are 4 models with overlapping nominal flow ranges from 200 g/h up to 600 kg/h (full scale value), each offering "multi-range" functionality: factory calibrated ranges can be rescaled by the user, maintaining the original accuracy specs. Both meters and controllers are equipped with an IP65 weatherproof housing and are available with ATEX approval for use in Zone 2 hazardous areas.

Fields of application

CORI-FLOW® instruments are applied in process fluid measurement or control systems in food, (petro-) chemical and pharmaceutical industries, in fermentation installations, in semiconductor processing and in fuel cell technology. Some typical examples of applications are described further on in this brochure.

General CORI-FLOW® features

- > Direct mass flow measurement
- > Independent of fluid properties
- > Integrated PID controller for control valve or pump
- > Fast response time
- > High accuracy, excellent repeatability
- > Compact, IP65 housing
- > ATEX approval Cat.3, Zone 2
- > Option: bidirectional measurement

Digital features

- > DeviceNet™, PROFIBUS-DP®, Modbus-RTU or FLOW-BUS slave
- > RS232 interface
- > Other fieldbus options on request
- > Alarm and (batch) counter functions




Bronkhorst
CORI-TECH

CORI-FLOW[®] for Liquids and Gases

Measuring principle

The CORI-FLOW[®] contains two parallel tube loops, forming part of an oscillating system. When a fluid flows through the tubes, Coriolis forces cause a variable phase shift between the loops, which is detected by sensors and fed into the integrally mounted pc-board. The resulting output signal is strictly proportional to the real mass flow rate.



Technical specifications

Performance flow sensor	
Accuracy	Liquid : 0,2% of rate + zero stability, range 20:1 Gas : 0,5% of rate + zero stability, range 50:1
Smallest Full Scale flow rates (values in kg/h)	
	M53 M54 M55
Max. flow FS	10 100 600
Min. flow FS Liquids	0,5 5 20
Min. flow FS Gases	1 10 50
Recommended min. flow	0,05 0,2 0,5
Zero stability	< 0,010 < 0,050 < 0,100
Repeatability	: 0,1% of rate (based on digital output)
Mounting position	: preferred mounting position on liquid service upside down
Operating limits flow controller	
Control range	: 2...100% (with elastomeric seat)
Auto shut off	: valve closes when setpoint drops below 1,6%
Liquids and Gases	: any clean, homogeneous liquid or gas compatible with AISI 316 (or Hastelloy-C22 as an option)
Differential pressure mass flow controller	: recommended ΔP across control valve at least 50% of total ΔP for liquids and gases.
Settling time	: approx. 0,5 s

Mechanical	
Process connections	: std. 1/4" face seal male, or 1/8", 1/4" or 6 mm OD compression type; other on request
Material of construction (wetted parts)	: stainless steel AISI 316 or equivalent; option for M52 / M53 / M54: Hastelloy-C22
Weight	: meter: approx. 3,1 kg meter + integral valve: 4,4 kg (max.)
Ingress protection	: IP 65 (weatherproof) for meter; for controller on request
Leak integrity	: < 2×10^{-9} mbar l.s ⁻¹ He
Pressure test	: 1,5 times max. stated operating pressure prevailing at customer
Max. operating pressure	: 100 bar
Temperature range (ambient + fluid)	: 0...70°C for standard version, 0...120°C with remote electronics, 130°C \leq 1 hour allowed for CIP
Electrical	
Power supply	: +15...24 Vdc \pm 10%; (DeviceNet [™] +24 Vdc only)
Consumption electronics	: approx. 80 mA at 15 Vdc
Consumption valve (if present)	: 250 mA (max) at 15 Vdc
Output signal	analog : 0...5 (10) Vdc; 2 kOhm min. load 0 (4)...20 mA (sourcing); 375 Ohm max. load digital : Profibus-DP [®] , DeviceNet [™] , FLOW-BUS, RS232, Modbus, LonWorks
Command signal	analog : 0...5 (10) Vdc; 424 kOhm load 0 (4)...20 mA (sinking); 250 Ohm load digital : Profibus-DP [®] , DeviceNet [™] , FLOW-BUS, RS232, Modbus, LonWorks
Electr. connection	: male, 8-pin Amphenol for power, analog I/O and RS232 option : standard M12 connector for Profibus-DP [®] (female) or DeviceNet [™] /FLOW-BUS (male)/Modbus (male)
CE approved design	



CORI-FLOW[®] Mass Flow Meter with pressure actuated control valve

CORI-FLOW[®] mass flow meter/controller



Flow capacity liquid

Basic model	DN (mm)	Nominal Flow**	Capacities (kg/h)													
			0,5	1,0	2,0	5,0	10	20	50	100	200	500	600			
M53	1	5 kg/h	•	•	•	n	•	•	•	•	•	•	•	•	•	•
M54	2	50 kg/h				•	•	•	n	•	•	•	•	•	•	•
M55	4	500 kg/h							•	•	•	•	•	n	•	


* Nominal flow: mass flow rate of liquid at a pressure drop of approx. 1 bar and based on reference conditions of water at approx. 20°C.
 ** Lowest recommended value for optimal performance is 20 g/h.

Dimensions (mm)



M50-Series Mass Flow Meter




Pressure drop liquid (H₂O)





M50C2-Series Mass Flow Controller



Pressure P₁ vs. mass flow for Air (P₂ = 1 bara)



M50C4-Series Mass Flow Controller





* Capacity based on air flow measurement: capacity shown increases with pressure; max. allowable pressure is 100 bara.

Table 1 (Z-values in mm)

Connections (in/out)	M50	M50C2/ M50C51	M50C4
1/8" compression type	201	267	-
1/8" face seal male	194	260	-
1/4" compression type	204	270	306
1/4" face seal male	202	267	301
1/4" face seal female	202	267	-
6 mm compression type	204	270	306

M50C51-Series Mass Flow Controller



Technical specifications and dimensions subject to change without notice.
 Dimensional drawings for other MFCs available on request.

CORI-FLOW[®] Applications

Applications

The CORI-FLOW[®] is suitable for application in industrial environment, laboratories and OEM installations in the following markets (typically):


- > Surface treatment,
- > Energy (fuel cells),
- > Semiconductor industry,
- > Chemical industry,
- > Pharmaceutical industry,
- > Food industry,
- > Optical fibre industry, etc.

Critical gas measurement

Fluids like carbon dioxide (CO₂) and ethylene (C₂H₄) are difficult to measure when they are in the interphase stage between being a liquid and a gas. This occurs at temperatures >20°C when pressure ranges from approx. 20 bara to approx. 60...95 bara (depending on temperature).

Under these conditions, physical properties like density (ρ) and heat capacity (C_p) change very rapidly which makes an accurate mass flow measurement, based on the thermal principle, very difficult.


CORI-FLOW[®] offers a solution here because of the true mass flow measurement, independent of physical properties. The true mass flow of the molecules is measured, regardless of whether the fluid is in gas phase, in liquid phase or indeed somewhere in between. Experiences in the field have proven that this principle of measuring is very accurate and reliable.



CORI-FLOW[®] with pump control, Profibus-DP operated

By utilising the integrated PID-control function on the CORI-FLOW[®] meter, a desired mass flow can be controlled with either a traditional proportional valve or now, more commonly, with a pump as the actuator. The PID-control to the pump can either be via a direct analogue signal (0...10 V, 0...15 V, 0...20 mA, 4...20 mA) or can be via a voltage/current to frequency converter if this feature is available. The maximum power load for the PID-controller output is ~3.75 Watt. PID-settings for optimal pump control can be set using FlowPlot, a Bronkhorst tooling program. Most commonly this will be performed in the factory, however, in line with the Bronkhorst Total Service Concept it is also possible to do this on site.

CORI-FLOW[®] instruments can be operated using normal analog signals or via digital interfaces such as RS232 or fieldbus communication. Profibus-DP is popular within the process industry as it offers a straight forward connection between a master, a PC or PLC (e.g. Siemens S7-300/400) and its slave devices. Within such a system, the CORI-FLOW[®] instrument would act as one of the slave devices and as such would have its control behaviour influenced by the master device. This offers high flexibility in mass flow control.



CORI-FLOW[®] Applications

CORI-FILL[®] Compact Fluid Dosage Assembly

Each Compact Fluid Dosing Assembly consists of a Coriolis Mass Flow Meter of the CORI-FLOW[®] or mini CORI-FLOW[®] series and a valve or a pump. The onboard PID-controller of the flow meter will be optimized for controlling the valve or the pump and enables an immediate start of dosage after connecting power and fluid accessories. Just enter the desired flow or batch at the operation module (or remotely by computer) and the compact unit will dose true mass flow, for example independent of ambient temperature and back pressure.


Using the integrated CORI-FILL[®] technology, the Coriolis meter's totalizer is capable of highly accurate batch dosage. It also ensures the actuator will react as soon as the batch has (almost) been reached.

Normally several components would be needed to achieve this:

- > Flowmeter
- > Valve/pump
- > Batchcounting module/PLC
- > Software handling these items
- > Weighing scales

CORI-FILL[®] offers all this functionality in one component, in one assembly and from one supplier, without the need of complex programming of additional hardware.

More information about CORI-FILL[®] applications can be found at www.cori-fill.com





CORI-FLOW[®] instruments can be used to directly control proportional valves, shut-off valves or pumps, using their integrated PID-controller. Thanks to the CORI-FILL[®] technology, highly accurate filling applications are possible using the integrated batch-counter.

Using our standard instruments, maximum flow speed is about 1000 kg/h. This enables filling of 278 gram in 1 second or 16,68 kg per minute. For higher or lower flow rates please consult factory.



RS232 / FLOW-BUS

DDE



Model number identification MFM and MFC

M5N - AN(I) - A A A - NN - A - A

Mass flow meter

M53	Nominal range	5 kg/h
M54	Nominal range	50 kg/h
M55	Nominal range	500 kg/h

Control valve

C0 (I)	Low Flow control valve (nc) PN100	gas; Kv-max = $6,6 \times 10^{-2}$
C1 (I)	Low Flow control valve (no) PN100	gas; Kv-max = $6,6 \times 10^{-2}$
C2 (I)	Low Flow control valve + purge connection (nc) PN100	liquid; Kv-max = $2,3 \times 10^{-3}$
C3 (I)	Low Flow control valve + purge connection (no) PN100	liquid; Kv-max = $2,3 \times 10^{-3}$
C4 (I)	Medium Flow control valve (nc) PN100	gas or liquid; Kv-max = $3,0 \times 10^{-1}$
C5I	Medium Flow control valve (nc) PN100, IP65	gas or liquid; Kv-max = $6,6 \times 10^{-2}$

add 'I' for IP65 coil on control valve

PC-board

A	with RS232 and analog I/O	(nc)	controller-function
B	with RS232 and analog I/O	(no)	controller-function
D	with RS232 and DeviceNet I/O	(nc)	controller-function
E	with RS232 and DeviceNet I/O	(no)	controller-function
M	with RS232 and Modbus I/O	(nc)	controller-function
N	with RS232 and Modbus I/O	(no)	controller-function
P	with RS232 and Profibus I/O	(nc)	controller-function
Q	with RS232 and Profibus I/O	(no)	controller-function
R	with RS232 and FLOW-BUS I/O	(nc)	controller-function
S	with RS232 and FLOW-BUS I/O	(no)	controller-function

Output

A	0...5 V
B	0...10 V
F	0...20 mA sourcing
G	4...20 mA sourcing

Supply voltage

D	+ 15...24 Vdc
---	---------------

Connections (in/out)

1	1/8"	OD compression type
2	1/4"	OD compression type
3	6 mm	OD compression type
4	12 mm	OD compression type
5	1/2"	OD compression type
7	1/4"	Face seal female
8	1/4"	Face seal male
9	Other	

Internal seals

0	None (sensors)
V	Viton (valves for gas)
E	EPDM
K	Kalrez-6375

Material

S	Stainless steel
H	Hastelloy-C22



Bronkhorst Cori-Tech B.V.

Nijverheidsstraat 2-6

7261AK Ruurlo The Netherlands

Tel. +31 573 458890 Fax. +31 842 292375

Email: info@bronkhorst-cori-tech.com

Internet: www.bronkhorst-cori-tech.com

